

Datasheet F-110C

Mass Flow Meter for Gases

> Introduction

Bronkhorst High-Tech model F-110C Mass Flow Meters (MFMs) are suited for precise measurement of virtually all conventional process gases. The MFM consists of a thermal mass flow sensor and a microprocessor based pc-board with signal and fieldbus conversion and a PID controller for optional mass flow control by means of a separately mounted control valve. The mass flow, expressed in normal millilitres per minute or per hour, is provided as analog signal or digitally via RS232 or fieldbus. The flow range and wetted materials are determined depending of the type of gas and the process conditions of the application.

Although all specifications in this datasheet are believed to be accurate, the right is reserved to make changes without notice or obligation.



EL-FLOW Mass Flow Meter model F-110C

> Technical specifications

Measurement / control system

Accuracy (incl. linearity) (Based on actual calibration)	: FS > 5 ml _n /min: ± 0,5 % Rd plus ± 0,1% FS; FS 3...5 ml _n /min: ± 1 % FS; FS < 3 ml _n /min: ± 2 % FS
Turndown	: 1 : 50 (in digital mode up to 1:187,5)
Multiple fluid capability	: • storage of max. 8 calibration curves • optional Multi Gas / Multi Range functionality up to 10 bar abs
Repeatability time (t _{63%})	: < ± 0,2% Rd Response : FS < 3 ml _n /min: 2 sec FS > 3 ml _n /min: 1...2 sec
Temperature range sensitivity	: -10...+70°C Temperature : zero: < ± 0,05% FS/°C (± 0,05% Rd/°C)
Leak integrity (outboard)	: < 2 x 10 ⁻⁹ mbar l/s He
Attitude sensitivity	: max. error at 90° off horizontal 0,2% FS at 1 bar, typical N ₂
Warm-up time	: 30 min. for optimum accuracy 2 min. for accuracy ± 2% FS

Mechanical parts

Material (wetted parts)	: stainless steel 316L or comparable
Pressure rating	: 100 bar abs
Process connections	: compression type or face seal male
Seals	: standard : Viton; options: EPDM, Kalrez
Ingress protection (housing)	: IP40

Electrical properties

Power supply	: +15...24 Vdc ±10%
Power consumption	: max. 320 mA;
Analog output	: add 50 mA for Profibus, if applicable
Analog setpoint (for MFM + control valve)	: 0...5 (10) Vdc, min. load impedance > 2 kΩ 0 (4)...20 mA (sourcing), max. load impedance < 375 Ω
Digital communication	: standard RS232 ; options: Profibus-DP®, DeviceNet™, EtherCAT®, Modbus-RTU/ASCII, FLOW-BUS

> Ranges (based on Air)

Model	minimum	nominal	maximum
F-110C-002	0,014...0,7 ml _n /min	0,014...2 ml _n /min	0,014...5 ml _n /min
F-110C-005	0,6...3 ml _n /min	0,6...5 ml _n /min	0,6...9 ml _n /min

Intermediate ranges are available

По вопросам продаж и поддержки обращайтесь:


Волгоград +7 (8442) 45-94-42
Екатеринбург +7 (343) 302-14-75
Ижевск +7 (3412) 20-90-75
Казань +7 (843) 207-19-05

Краснодар +7 (861) 238-86-59
Красноярск +7 (391) 989-82-67
Москва +7 (499) 404-24-72
Ниж.Новгород +7 (831) 200-34-65

Новосибирск +7 (383) 235-95-48
Омск +7 (381) 299-16-70
Пермь +7 (342) 233-81-65
Ростов-на-Дону +7 (863) 309-14-65

Самара +7 (846) 219-28-25
Санкт-Петербург +7 (812) 660-57-09
Саратов +7 (845) 239-86-35
Сочи +7 (862) 279-22-65

> Model number identification




> Thermal mass flow measuring principle


The heart of the thermal mass flow meter/controller is the sensor, that consists of a stainless steel capillary tube with resistance thermometer elements. At EL-FLOW model F-110C the total gas flows through this sensor, and is warmed up heating elements. Consequently the measured temperatures T_1 and T_2 drift apart. The temperature difference is directly proportional to mass flow through the sensor.

> State of the art digital design

Todays EL-FLOW® series are equipped with a digital pc-board, offering high accuracy, excellent temperature stability and fast response. The basic digital pc-board contains all of the general functions needed for measurement and control. In addition to the standard RS232 output the instruments also offer analog I/O. Furthermore, an integrated interface board provides DeviceNet™, Profibus-DP®, Modbus-RTU or FLOW-BUS protocols.




Functional scheme of thermal mass flow sensor (F-110C)




Functional scheme of the digital PC-board


> Hook-up diagram for analog or RS232 communication



> Hook-up diagrams for fieldbus communication




> Dimensions (mm) and weight (kg)



Dimension table adapters (RS-type)

Compression type	1/8"BSPP	Size A
adapter 3 mm	OD	25.3
adapter 6 mm	OD	27.6
adapter 8 mm	OD	28.6
adapter 1/16"	OD	20.6
adapter 1/8"	OD	25.3
adapter 1/4"	OD	27.6
adapter 3/8"	OD	29.5
Face-seal male	A	
adapter 1/8" inlet		17.8
adapter 1/4" inlet		23.7



*) Dimension A is typical finger-tight.

> Options and accessories

- Multi-Gas / Multi-Range option, with free configuration software.
- Free software support for operation, monitoring, optimizing or to interface between digital instruments and windows software.



- IN-LINE filters for protection against particulates



- BRIGHT compact local Readout/Control modules
- E-5700 / E-7000 Power Supply



- Interconnecting cables for power and analog/digital communication
- PiPS Plug-in Power Supply



> Alternatives

- IQ⁺FLOW, world's smallest Mass Flow Meter (smallest range 0,2...10 ml_n/min)



- LOW-ΔP-FLOW series MFM for low pressure drop applications or corrosive gas service (smallest range 0,2...10 ml_n/min)



- Metal Sealed MFM for Semiconductor or other high purity applications (smallest range 0,1...5 ml_n/min)



По вопросам продаж и поддержки обращайтесь:

Волгоград +7 (8442) 45-94-42
Екатеринбург +7 (343) 302-14-75
Ижевск +7 (3412) 20-90-75
Казань +7 (843) 207-19-05

Краснодар +7 (861) 238-86-59
Красноярск +7 (391) 989-82-67
Москва +7 (499) 404-24-72
Ниж.Новгород +7 (831) 200-34-65

Новосибирск +7 (383) 235-95-48
Омск +7 (381) 299-16-70
Пермь +7 (342) 233-81-65
Ростов-на-Дону +7 (863) 309-14-65

Самара +7 (846) 219-28-25
Санкт-Петербург +7 (812) 660-57-09
Саратов +7 (845) 239-86-35
Сочи +7 (862) 279-22-65

сайт: bronkhorst.pro-solution.ru | эл. почта: brk@pro-solution.ru
телефон: 8 800 511 88 70